



VE112L

**Enclosure,vector,IP5x,12Modules,version Austria**

**Technical Features**

**Voltage**

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Equipment**

|                            |    |
|----------------------------|----|
| Number of rails            | 1  |
| Number of rows             | 1  |
| Number of section in width | 1  |
| With lock                  | No |
| Has neutral terminal block | No |

**Capacity**

|                   |    |
|-------------------|----|
| Number of modules | 12 |
|-------------------|----|

**Functions**

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

**Dimensions**

|        |        |
|--------|--------|
| Height | 302 mm |
| Width  | 310 mm |
| Depth  | 151 mm |

**Cover, door**

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
| Number of locks         | 0 |

**Dimensions**

|                       |    |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

**Cover, door**

|                           |     |
|---------------------------|-----|
| Door/cover is transparent | Yes |
|---------------------------|-----|

**Connection**

|                          |    |
|--------------------------|----|
| Number of conduit inlets | 12 |
|--------------------------|----|

**Materials**

|          |                  |
|----------|------------------|
| Material | Polystyrene (PS) |
| RAL code | 7035             |
| Colour   | Light grey       |

**Equipment**

|                             |    |
|-----------------------------|----|
| Has earthing terminal block | No |
| Has mounting plate          | No |

**Materials**

|                       |    |
|-----------------------|----|
| Ultraviolet-resistant | No |
|-----------------------|----|

**Safety**

|                               |                              |
|-------------------------------|------------------------------|
| Protection class              | Isolation class II           |
| Impact resistance IK          | IK08                         |
| Ingress Protection (IP) class | IP65                         |
| Locking type                  | Snap on lock<br>Without lock |
| Glow wire test                | 750 °C                       |