



VE112U

### Enclosure,vector,IP5x,12M

#### Technical Features

##### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Electric current

Rated current	63 A
---------------	------

##### Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

##### Capacity

Number of modules	12
-------------------	----

##### Functions

With conduit inlets	Yes
---------------------	-----

##### Dimensions

Height	302 mm
Width	310 mm
Depth	151 mm

##### Cover, door

Number of cabinet doors	1
Number of locks	0

##### Dimensions

Number of width units	12
-----------------------	----

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Connection

Number of conduit inlets	12
--------------------------	----

##### Materials

Material	Plastic
RAL code	7035
Colour	Light grey

##### Equipment

Has earthing terminal block	No
Has mounting plate	No

##### Materials

Ultraviolet-resistant	No
-----------------------	----

##### Safety

Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65
Locking type	Snap on lock Without lock
Glow wire test	750 °C

Sustainability

RoHS conform	Yes
--------------	-----