



WXA696

Lamp for switch gallery 12/24V red

Technical Features

Voltage

Nominal voltage	24 - 24 V
-----------------	-----------

Electric current

Rated current	0 A
---------------	-----

Dimensions

Height	17.10 mm
Width	45 mm
Depth	17.55 mm

Power

Current consumption	1.10 mA
---------------------	---------

Materials

Colour	Red
--------	-----

Lighting

Type of lamp	LED
--------------	-----

Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

Suitable for

Hager gallery	
---------------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes