



WXA696

Lamp for switch gallery 12/24V red

Technical Features

Voltage

Nominal voltage 24 - 24 V

Electric current

Rated current 0 A

Dimensions

Height 17.10 mm

Width 45 mm

Depth 17.55 mm

Power

Current consumption 1.10 mA

Materials

Colour Red

Lighting

Type of lamp LED

Use conditions

Operating temperature -10 - 35 °C

Suitable for

gallery

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes