



VE110F

Enclosure, vector, IP5x, 10M

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block No

Capacity

Number of modules 10

Functions

With conduit inlets Yes

Dimensions

Height 210 mm

Width 237 mm

Depth 114 mm

Cover, door

Number of cabinet doors 1

Number of locks 0

Dimensions

Number of width units 10

Cover, door

Door/cover is transparent No

Connection

Number of conduit inlets 6

Connectivity

Mounting type Screw mounting

Materials

Material Polystyrene (PS)

RAL code 7035

Colour Light grey

Equipment

Has earthing terminal block Yes

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP65

Safety

Locking type	Snap on lock Without lock
Glow wire test	750 °C

Sustainability

RoHS conform	Yes
--------------	-----