



VE103L

Enclosure,vector,IP5x,3Modules,version Austria

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block No

Capacity

Number of modules 3

Functions

With conduit inlets Yes

Dimensions

Height 175 mm

Width 111 mm

Depth 93 mm

Cover, door

Number of cabinet doors 1

Number of locks 0

Dimensions

Number of width units 3

Cover, door

Door/cover is transparent Yes

Connection

Number of conduit inlets 2

Materials

Material Polystyrene (PS)

RAL code 7035

Colour Light grey

Equipment

Has earthing terminal block No

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP65

Locking type Snap on lock
Without lock

Glow wire test 750 °C

Sustainability

RoHS conform

Yes