



VE103L

Enclosure,vector,IP5x,3Modules,version Austria

### Technical Features

#### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	63 A
---------------	------

#### Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	3
-------------------	---

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	175 mm
Width	111 mm
Depth	93 mm

#### Cover, door

Number of cabinet doors	1
Number of locks	0

#### Dimensions

Number of width units	3
-----------------------	---

#### Cover, door

Door/cover is transparent	Yes
---------------------------	-----

#### Connection

Number of conduit inlets	2
--------------------------	---

#### Materials

Material	Polystyrene (PS)
RAL code	7035
Colour	Light grey

#### Equipment

Has earthing terminal block	No
Has mounting plate	No

#### Materials

Ultraviolet-resistant	No
-----------------------	----

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65
Locking type	Snap on lock Without lock
Glow wire test	750 °C

Sustainability	
RoHS conform	Yes