



VE103U

Enclosure,vector, IP65, 3M

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No

Capacity

Number of modules	3
-------------------	---

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	175 mm
Width	111 mm
Depth	93 mm

Cover, door

Number of cabinet doors	1
Number of locks	0

Dimensions

Number of width units	3
-----------------------	---

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Connection

Number of conduit inlets	2
--------------------------	---

Materials

Material	Plastic
RAL code	7035
Colour	Light grey

Equipment

Has mounting plate	No
--------------------	----

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65
Locking type	Snap on lock Without lock
Glow wire test	750 °C

Sustainability

RoHS conform	Yes
--------------	-----