



WNE122B



cubyko Double horizontal socket 2P+E screwless wall mounted white IP55

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Dimensions

Height 76 mm

Width 147 mm

Depth 22.80 mm

Number of units 2

Built-in depth flush-mounted boxes 0 mm

Built-in depth 0 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Surface mounting

Mounting-/Connection Position Horizontal

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid Yes

With round protective earth pin Yes

With signal lamp No

With lock No

Accessories

Has labelling field No

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 2

Safety

With enhanced contact protection Yes

Impact resistance IK IK07

Ingress Protection (IP) class IP55

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

cubyko

Sustainability

Halogen free	Yes
RoHS conform	Yes