



VE106F

**Enclosure, vector, IP5x, 6M**

**Technical Features**

**Voltage**

Nominal voltage	400 - 400 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	6
-------------------	---

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	190 mm
Width	165 mm
Depth	113 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	0

**Dimensions**

Number of width units	6
-----------------------	---

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Connection**

Number of conduit inlets	3
--------------------------	---

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Materials**

Material	Polystyrene (PS)
RAL code	7035
Colour	Light grey

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Materials**

Ultraviolet-resistant	No
-----------------------	----

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65

**Safety**

Locking type	Snap on lock Without lock
Glow wire test	750 °C

**Sustainability**

RoHS conform	Yes
--------------	-----