



VE106F

**Enclosure,vector, IP5x, 6M**

**Technical Features**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Surface mounting

**Electric current**

Rated current 63 A

**Equipment**

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block No

**Capacity**

Number of modules 6

**Functions**

With conduit inlets Yes

**Dimensions**

Height 190 mm

Width 165 mm

Depth 113 mm

**Cover, door**

Number of cabinet doors 1

Number of locks 0

**Dimensions**

Number of width units 6

**Cover, door**

Door/cover is transparent No

**Connection**

Number of conduit inlets 3

**Connectivity**

Mounting type Screw mounting

**Materials**

Material Polystyrene (PS)

RAL code 7035

Colour Light grey

**Equipment**

Has earthing terminal block Yes

Has mounting plate No

**Materials**

Ultraviolet-resistant No

**Safety**

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP65

**Safety**

Locking type	Snap on lock Without lock
Glow wire test	750 °C

**Sustainability**

RoHS conform	Yes
--------------	-----