



VE106U

Enclosure,vector,IP5x, 6M

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

Has neutral terminal block	No
----------------------------	----

Capacity

Number of modules	6
-------------------	---

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	190 mm
--------	--------

Width	165 mm
-------	--------

Depth	113 mm
-------	--------

Cover, door

Number of cabinet doors	1
-------------------------	---

Number of locks	0
-----------------	---

Dimensions

Number of width units	6
-----------------------	---

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	3
--------------------------	---

Materials

Material	Plastic
----------	---------

RAL code	7035
----------	------

Colour	Light grey
--------	------------

Equipment

Has earthing terminal block	No
-----------------------------	----

Has mounting plate	No
--------------------	----

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
------------------	--------------------

Impact resistance IK	IK07
----------------------	------

Ingress Protection (IP) class	IP65
-------------------------------	------

Locking type	Snap on lock Without lock
--------------	------------------------------

Glow wire test	750 °C
----------------	--------

Sustainability	
RoHS conform	Yes