



VE106U

Enclosure,vector,IP5x, 6M

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	6
-------------------	---

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	190 mm
Width	165 mm
Depth	113 mm

Cover, door

Number of cabinet doors	1
Number of locks	0

Dimensions

Number of width units	6
-----------------------	---

Cover, door

Door/cover is transparent	No
Cabinet door type	Single door

Connection

Number of conduit inlets	3
--------------------------	---

Materials

Material	Plastic
RAL code	7035
Colour	Light grey

Equipment

Has earthing terminal block	No
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65
Locking type	Snap on lock Without lock
Glow wire test	750 °C

Safety

Protection class with door	IP65
----------------------------	------

Sustainability

RoHS conform	Yes
--------------	-----
