



WGMS113SAS

13A SINGLE SWITCHED SOCKET, AS

Technical Features

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Electric current

| | |
|----------------|------|
| Output current | 0 mA |
| Rated current | 13 A |

Voltage

| | |
|----------------|-------|
| Output voltage | 0-0 V |
|----------------|-------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20 - 45 °C |
|-----------------------|-------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Power

| | |
|---------------------------|-----|
| Output power | 0 W |
| Power consumption standby | 0 W |

Materials

| | |
|--|--------------------|
| Colour | Aurora silver |
| Surface finish | Matt |
| Material | Polycarbonate (PC) |
| Treatment | Coated |
| Contains recycled material (% of total plastic weight) | 0 % |

Dimensions

| | |
|--------|-------|
| Height | 31 mm |
| Width | 86 mm |
| Depth | 18 mm |

Cable

| | |
|--------------|-----|
| Cable length | 0 m |
|--------------|-----|

Dimensions

| | |
|------------------------------------|-------|
| Built-in depth flush-mounted boxes | 35 mm |
| Built-in depth | 18 mm |

Connection

| | |
|--|--------------------------|
| Connector/plug type | British Standard |
| Cross-section flexible conductor without wire end sleeve | 0.08 - 4 mm ² |
| Number of conduit inlets | 0 |

Installation, mounting

| | |
|-------------------------------|----------------|
| Mounting on | Flush mounting |
| Mounting-/Connection Position | Back |

Connectivity

| | |
|-------------------------|------------------|
| Type of connection | Screw terminal |
| With claw mounting | No |
| Mounting type | Screw mounting |
| Connector/plug type USB | British Standard |

Equipment

| | |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert | Yes |
| With hinged lid | No |
| With round protective earth pin | No |
| With signal lamp | No |

Equipment

| | |
|-----------|----|
| With lock | No |
|-----------|----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

| | |
|-------------------|------|
| Pre-equipped with | None |
|-------------------|------|

Capacity

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Safety

| | |
|----------------------------------|----|
| With enhanced contact protection | No |
|----------------------------------|----|

| | |
|----------------------|------|
| Impact resistance IK | IK02 |
|----------------------|------|

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
|---------------------------|----|

| | |
|------------------------|----|
| With function lighting | No |
|------------------------|----|

Identification

| | |
|--------------|----|
| With imprint | No |
|--------------|----|

Suitable for

| | |
|-------|--|
| shark | |
|-------|--|

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|
