



HWX006H

**Spring charging motor 415-450V AC 50/60Hz HW1 (MO)**

**Technical Features**

**Electric current**

Rated current	0.50 A
---------------	--------

**Voltage**

Type voltage supply	AC
Rated insulation voltage $U_i$	450 V
Rated impulse withstand voltage $U_{imp}$	6000 V
Command voltage AC	415 - 450 V

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes