



HWX006H

Spring charging motor 415-450V AC 50/60Hz HW1 (MO)

Technical Features

Electric current

Rated current	0.50 A
---------------	--------

Voltage

Type voltage supply	AC
Rated insulation voltage Ui	450 V
Rated impulse withstand voltage Uimp	6000 V
Command voltage AC	415 - 450 V

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes