



LFF4009007030

**Liféa trunking 40x90 with coupling and 2 cable retainer, grey**

**Technical Features**

**Dimensions**

Height	40 mm
Width	90 mm
Length	2000 mm
Inner cross-section	2650 - 2650 mm <sup>2</sup>

**Capacity**

Max. number of cables (Ø11mm, 50% filled, without devices)	14
--	----

**Materials**

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	7030
Colour	Stone grey

**Safety**

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

**Standards**

Suitable for functional integrity according to DIN4102-12	No
---	----

**Use conditions**

Operating temperature	-5 - 60 °C
-----------------------	------------

**Connectivity**

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

**Equipment**

Number of partitions	0
Number of pluggable partitions	1
Cable retaining clip included	Yes
With protective film	No

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes