



VF9101SPD

### Volta 3Row 7W 1RCD - 2x6A Ltg. RCBOs SPD

#### Technical Features

##### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

##### Electric current

Rated current	63 A
---------------	------

##### Equipment

Number of rails	3
Number of rows	3
With lock	No
Has neutral terminal block	Yes

##### Capacity

Number of modules	36
-------------------	----

##### Dimensions

Height	630.50 mm
Width	348 mm
Depth	94.50 mm
Built-in width	314 mm

##### Cover, door

Number of cabinet doors	1
-------------------------	---

##### Dimensions

Built-in depth	89 mm
----------------	-------

##### Cover, door

Number of locks	0
-----------------	---

##### Dimensions

Number of width units	12
-----------------------	----

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Materials

Material	Plastic
RAL code	9010
Colour	Pure white

##### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

##### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Snap on lock
Glow wire test	650 °C