



75143835



IP20

**KNX glass sensor 3gang comf, intg bus coupling unit, KNX-TS sensor, glass black**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Use conditions**

Operating temperature -5 - 45 °C

**Functions**

With room temperature controller Yes

**Power**

Current consumption 12.50 mA

**Dimensions**

Built-in depth 24.20 mm  
 Built-in depth flush-mounted boxes 27 mm  
 Height 160 mm  
 Width 86 mm  
 Depth 37.70 mm

**Equipment**

Number of actuation points 6

**Controls and indicators**

With LED indication Yes

**Materials**

Colour Black  
 RAL code 9005  
 Material Glass  
 Surface finish Glossy

**Accessories**

Has labelling field No

**Screen**

With display No

**Texts**

Function For switch, push-button, dimmer and shutter functions  
 Blocking function for sensor surface e.g. for cleaning the glass surface  
 Installation mode For vertical mounting  
 Temperature Additional connection for external temperature sensor  
 Integrated temperature sensor for operation as controller extension unit  
 Temperature measurement via internal Temperature sensor or external communication object

**Sustainability**

REACH-SVHC free Yes  
 RoHS conform Yes