



JN8E02S

### Technical Features

#### Dimensions

Height	179 mm
Width	846 mm
Depth	205 mm
Thickness of sidewall	1.50 mm

#### Safety

Ingress Protection (IP) class	IP41
Protection class	Isolation class I
Locking type	Special tool Without lock
Impact resistance IK	IK05

#### Equipment

Number of flange plate openings	2
---------------------------------	---

#### Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

#### Materials

Colour	Grey white
RAL code	9002
Treatment	Varnished
Material	Steel
Surface finish	Matt

#### Cover, door

Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	No

#### Voltage

Nominal voltage	415 - 415 V
-----------------	-------------

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes