



VML\_SIZE\_7

## 16 Way HI Cf 100A Switch 2\*100A 30mA Round KO

### Technical Features

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Functions

Has protection main switch	Yes
Overvoltage protection	Yes

#### Capacity

Number of modules	16
-------------------	----

#### Electric current

Rated current	100 A
---------------	-------

#### Dimensions

Depth	100 mm
Height	245 mm
Width	476 mm

#### Cover, door

Interlockable	No
Door/cover is transparent	No

#### Materials

RAL code	9010
Colour	Pure white
Material	Steel

#### Connection

Number of accessible phases	1
-----------------------------	---

#### Scope of delivery

Number of earth leakage circuit breaker type A	2
Number of RCCB in enclosure	2

#### Equipment

Number of rows	1
Number of rails	1

#### Safety

Ingress Protection (IP) class	IP2XC
-------------------------------	-------