



VD112TT

Sm.distr.,VD/IC<sup>2</sup>,surface,1row,12M,IP40,MS-terminals,AUS,N+PE,transparent door

**Technical Features**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Surface mounting

**Electric current**

Rated current 63 A

**Equipment**

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block Yes

**Capacity**

Number of modules 12

**Functions**

With conduit inlets Yes

**Dimensions**

Height 200 mm

Width 292.50 mm

Depth 91 mm

**Cover, door**

Number of cabinet doors 1

Number of locks 0

**Dimensions**

Number of width units 12

**Cover, door**

Door/cover is transparent Yes

**Materials**

Material Plastic

RAL code 9010

Colour Pure white

**Equipment**

Has earthing terminal block Yes

Has mounting plate No

**Materials**

Ultraviolet-resistant No

**Safety**

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP40

Locking type Snap on lock  
Without lock

Glow wire test 650 °C

**Sustainability**

RoHS conform Yes