



WRSS81BSW

### 13A 1 Gang Double Pole Switched Socket Brushed Steel White Insert

#### Technical Features

##### Electric current

|               |      |
|---------------|------|
| Rated current | 13 A |
|---------------|------|

##### Voltage

|                 |             |
|-----------------|-------------|
| Rated voltage   | 250 V       |
| Nominal voltage | 250 - 250 V |

##### Materials

|                |                 |
|----------------|-----------------|
| Colour         | Stainless steel |
| Surface finish | Matt            |
| Material       | Stainless steel |
| Treatment      | Brushed         |

##### Dimensions

|        |          |
|--------|----------|
| Height | 86 mm    |
| Width  | 86 mm    |
| Depth  | 25.80 mm |

##### Installation, mounting

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Horizontal     |

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type      | Screw mounting |

##### Equipment

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert            | No               |
| With hinged lid                   | No               |
| With round protective earth pin   | No               |
| With signal lamp                  | No               |

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Functions

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

##### Texts

|            |                             |
|------------|-----------------------------|
| Imprint    | Without imprint             |
| Cover      | Full cover plate            |
| Wiring     | With earth connection       |
| Protection | Enhanced contact protection |

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |