



SVN121

Green LED Indicator light 230VAC

Technical Features

Capacity

Number of modules	1
-------------------	---

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated insulation voltage U_i	250 V
Rated impulse withstand voltage U_{imp}	4000 V
Rated operational voltage U_e	230 - 230 V
Type voltage supply	AC

Use conditions

Operating temperature	-20 - 50 °C
Storage/transport temperature	-40 - 80 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	0.75 - 6 mm ²
Cross-section rigid conductor	0.75 - 10 mm ²

Power

Total power loss under I_N	0.80 W
------------------------------	--------

Dimensions

Height	83 mm
Width	17.50 mm
Depth	62 mm

Lighting

Type of lamp	LED
--------------	-----

Connection

Type of lamp socket	Fix
---------------------	-----

Materials

Colour	Green
--------	-------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Power

Power per charging point	0 kW
--------------------------	------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes