



VF112PM

Small distributor,golf,flush,1row,12M,IP40,MS-terminal,N+PE,white door

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Flush mounting
-------------	----------------

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

Has neutral terminal block	Yes
----------------------------	-----

Capacity

Number of modules	12
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	293 mm
--------	--------

Width	352 mm
-------	--------

Depth	97.50 mm
-------	----------

Built-in height	257 mm
-----------------	--------

Built-in width	318 mm
----------------	--------

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	72 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Plastic
----------	---------

RAL code	9010
----------	------

Colour	Pure white
--------	------------

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Has mounting plate	No
--------------------	----

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
------------------	--------------------

Impact resistance IK	IK07
----------------------	------

Ingress Protection (IP) class	IP40
-------------------------------	------

Product Datasheet

VF112PM

Safety	
Locking type	Snap on lock
	Without lock
Glow wire test	650 °C
Sustainability	
RoHS conform	Yes