



16512069

Rocker f. accessible const., tactile symb. f. door,clearlens,R.1/R.3,p.white gl.

#### Technical Features

##### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

##### Materials

|                |               |
|----------------|---------------|
| Colour         | Polar white   |
| RAL code       | 9010          |
| Surface finish | Glossy        |
| Material       | Thermoplastic |
| Treatment      | Untreated     |

##### Dimensions

|        |          |
|--------|----------|
| Height | 57.80 mm |
| Width  | 57.80 mm |
| Depth  | 20 mm    |

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Clamp mounting |
|---------------|----------------|

##### Equipment

|                                |     |
|--------------------------------|-----|
| Monitoring window/light outlet | Yes |
|--------------------------------|-----|

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP44 |
| Impact resistance IK          | IK05 |

##### Texts

|                                  |                                                |
|----------------------------------|------------------------------------------------|
| Imprint                          | Without imprint                                |
| Installation mode                | Clamp fastening                                |
| Push button                      | Also for KNX applications: push-button, 1-gang |
| Rocker switch/rocker push-button | For illuminated rocker push-buttons            |

##### Suitable for

|     |  |
|-----|--|
| R.x |  |
|-----|--|

##### Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |