



HIB463M

Motorized transfer switch 4P 630A

Technical Features

Voltage

Rated operational voltage U <sub>e</sub>	380 - 415 V
--	-------------

Electric current

Rated current	630 A
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	50 kA

Power

Rated operational power under 400 V AC AC1	414000 W
--	----------

Architecture

Number of poles	4
Device construction type	Fixed built-in

Compatibility

Suitable for DIN Rail	No
Suitable for distribution board	Yes

Installation, mounting

Mounting on	Mounting plate
-------------	----------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes