



WBQP2SUSBAC-MW

UNI. Twin Socket + USB A+C MW

Technical Features

Electric current

Rated current	10 A
---------------	------

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
Surface finish	Matt
Material	Polycarbonate (PC)

Dimensions

Height	82 mm
Width	120 mm
Depth	50.80 mm
Built-in depth flush-mounted boxes	70 mm

Connection

Connector/plug type	Screw terminal
---------------------	----------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Mounting type	Screw mounting
Connector/plug type USB	AC

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
---------------------------	----

Texts

Imprint	Without imprint
Cover	Full cover plate
Protection	Yes

Suitable for

finesse	
---------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes