



EE960

Emergency light

Technical Features

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Operating temperature	0 - 40 °C
Storage/transport temperature	-5 - 60 °C

Connectivity

Mounting type	Clamp mounting Screw connection
---------------	------------------------------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Power

Total power loss under IN	1 W
---------------------------	-----

Dimensions

Height	70 mm
Width	54 mm
Depth	51 mm

Voltage

Rated operational voltage U _e	230 - 230 V
--	-------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes