



VM11010

Dual Row,10+14 Way Hi Integrity 100A Switch 2*100A 30mA Type RCCB Type 2 SPD

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
Overvoltage protection	Yes

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Capacity

Number of modules	24
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	102.50 mm
Height	480 mm
Width	364 mm
Thickness of sidewall	1 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	2
Number of RCCB in enclosure	2

Equipment

Number of rows	2
Number of rails	2
Extension possible	No
With socket outlet	No

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC

Sustainability

RoHS conform	Yes
--------------	-----