



VT24F

24M 2Row DIN Flush Metal BOX, No Door

Technical Features

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 230 - 415 V |
|-----------------|-------------|

Installation, mounting

| | |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

Equipment

| | |
|-----------------|---|
| Number of rails | 2 |
| Number of rows | 2 |

Capacity

| | |
|-------------------|----|
| Number of modules | 24 |
|-------------------|----|

Dimensions

| | |
|----------------|--------|
| Height | 464 mm |
| Width | 414 mm |
| Depth | 10 mm |
| Built-in width | 364 mm |
| Built-in depth | 60 mm |

Cover, door

| | |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

Dimensions

| | |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

Cover, door

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Connection

| | |
|--------------------------|----|
| Number of conduit inlets | 16 |
|--------------------------|----|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 9002 |
| Colour | Grey white |

Equipment

| | |
|--------------------|----|
| Has mounting plate | No |
|--------------------|----|

Safety

| | |
|----------------------|-------------------|
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |