



VT24S

### 24M 2Row DIN Surface Metal BOX, No Door

#### Technical Features

##### Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Equipment

Number of rails	2
Number of rows	2

##### Capacity

Number of modules	24
-------------------	----

##### Dimensions

Height	419 mm
Width	369 mm
Depth	71 mm
Built-in depth	70 mm

##### Cover, door

Number of locks	0
-----------------	---

##### Dimensions

Number of width units	12
-----------------------	----

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Connection

Number of conduit inlets	16
--------------------------	----

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Materials

Material	Steel
RAL code	9002
Colour	Grey white

##### Equipment

Has mounting plate	No
--------------------	----

##### Safety

Protection class	Isolation class I
Impact resistance IK	IK05

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes