



937722505



Control push-button, NO contact, red lens, Integro - Design Flow/Pure, anth m

#### Technical Features

##### Electric current

Momentary contact current	10 A
---------------------------	------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

Number of poles	1
-----------------	---

##### Materials

Colour	Anthracite
--------	------------

Surface finish	Matt
----------------	------

Material	Thermoplastic
----------	---------------

Treatment	Untreated
-----------	-----------

Transparent	No
-------------	----

##### Dimensions

Height	55.50 mm
--------	----------

Width	55.50 mm
-------	----------

Depth	24.10 mm
-------	----------

Built-in depth flush-mounted boxes	13 mm
------------------------------------	-------

##### Controls and indicators

Number of buttons	1
-------------------	---

Type of push button	Single push button
---------------------	--------------------

With feedback signal contact	No
------------------------------	----

##### Safety

Ingress Protection (IP) class	IP44
-------------------------------	------

Impact resistance IK	IK05
----------------------	------

##### Accessories

Has labelling field	No
---------------------	----

##### Texts

Imprint	Without imprint
---------	-----------------

Installation mode	For screw fastening
-------------------	---------------------

Lighting	With integral neon lamp For lighting and monitoring circuit
----------	--

Type of connection	With screw terminals
--------------------	----------------------

##### Suitable for

integro	
---------	--