



ST310

**Safety Transformer 20VA 24A**

**Technical Features**

**Voltage**

Output voltage	24 - 24 V
Output voltage 2	24 V
Rated operational voltage Ue	230 - 230 V
Rated insulation voltage Ui	4000 V

**Power**

Power consumption VA	20 VA
----------------------	-------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Use conditions**

Operating temperature	-20 - 35 °C
-----------------------	-------------

**Capacity**

Number of modules	4
-------------------	---

**Dimensions**

Height	85 mm
Width	70 mm
Depth	58 mm

**Safety**

Ingress Protection (IP) class	IP20
Temperature protection	Yes

**Equipment**

Is short-circuit protected	Yes
On/off switch	No

**Connection**

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>