



ST309

Safety Transformer 20VA 12V

Technical Features

Voltage

Output voltage	12 - 12 V
Output voltage 2	12 V
Rated operational voltage U _e	230 - 230 V
Rated insulation voltage U _i	4000 V

Power

Power consumption VA	20 VA
----------------------	-------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Use conditions

Operating temperature	-20 - 35 °C
-----------------------	-------------

Capacity

Number of modules	4
-------------------	---

Dimensions

Height	85 mm
Width	70 mm
Depth	58 mm

Safety

Ingress Protection (IP) class	IP20
Temperature protection	Yes

Equipment

Is short-circuit protected	Yes
On/off switch	No

Connection

Cross-section flexible conductor	4 mm ²
Cross-section rigid conductor	6 mm ²