




29532045



LED signal light, white lighting, R.1/R.3, black glossy

Technical Features

Voltage

Rated voltage 230 V

Power

Power absorbed 1 W

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour Black

RAL code 9005

Surface finish Glossy

Material Metal
Plastic

Treatment Untreated

Dimensions

Height 70 mm

Width 70 mm

Depth 50 mm

Connection

Conductor cross-section 2.50 - 2.50 mm²

Safety

Ingress Protection (IP) class IP20

Texts

Lighting Light colour cold white

Labelling Foils with imprint of symbols insertable

Imprint Without imprint

Suitable for

R.x / Serie 1930 / Serie Glas

Sustainability

REACH-SVHC free Yes

RoHS conform Yes