



47753522

SCHUKO soc.out. 2gang hor. hinged cover surface-mtd, W.1, p.white, matt, plastic

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Dimensions

Height 76 mm

Width 147 mm

Depth 63 mm

Built-in depth flush-mounted boxes 0 mm

Connection

Conductor cross-section 1.0 - 2.5 mm²

Installation, mounting

Mounting on Surface mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid Yes

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field No

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 2

Safety

With enhanced contact protection No

Impact resistance IK IK05

Ingress Protection (IP) class IP55

Functions

With orientation lighting No

With function lighting No

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
-------	------------------

Wiring	Inserts wired-through
--------	-----------------------

Protection	Without enhanced contact protection
------------	-------------------------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
----------	--

Sustainability

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----
