



WXPDP84

IP66 20A 1 Gang 1 Way Double Pole Switch

Technical Features

Installation, mounting

Mounting on Surface mounting

Frequency

Frequency 50 - 60 Hz

Materials

Colour Light grey

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 90 x 90 mm

Built-in depth 0 mm

Electric current

Rated current 20 A

Texts

Lighting Without lighting (cannot be illuminated)

Push button No

Imprint With clear terminal markings

Sustainability

REACH-SVHC free Yes

RoHS conform Yes