



VS18TVA

Small distributor, icos, surface, 1 row, IP40, 18M, MS-terminal, N+PE, transparent door

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	18
-------------------	----

Dimensions

Height	165 mm
Width	409 mm
Depth	92.50 mm

Cover, door

Number of cabinet doors	1
Number of locks	0

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Materials

Material	Plastic
RAL code	9010
Colour	White

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock
Glow wire test	650 °C

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes