



VS18TVA

Small distributor, icos, surface, 1 row, IP40, 18M, MS-terminal, N+PE, transparent door

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Equipment

| | |
|----------------------------|-----|
| Number of rails | 1 |
| Number of rows | 1 |
| With lock | No |
| Has neutral terminal block | Yes |

Capacity

| | |
|-------------------|----|
| Number of modules | 18 |
|-------------------|----|

Dimensions

| | |
|--------|----------|
| Height | 165 mm |
| Width | 409 mm |
| Depth | 92.50 mm |

Cover, door

| | |
|-------------------------|---|
| Number of cabinet doors | 1 |
| Number of locks | 0 |

Dimensions

| | |
|-----------------------|----|
| Number of width units | 18 |
|-----------------------|----|

Cover, door

| | |
|---------------------------|-----|
| Door/cover is transparent | Yes |
|---------------------------|-----|

Materials

| | |
|----------|---------|
| Material | Plastic |
| RAL code | 9010 |
| Colour | White |

Equipment

| | |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate | No |

Safety

| | |
|-------------------------------|--------------|
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP40 |
| Locking type | Snap on lock |
| Glow wire test | 650 °C |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |