



VS18TVA

Small distributor, icos, surface, 1 row, IP40, 18M, MS-terminal, N+PE, transparent door

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	1
Number of rows	1
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	18
-------------------	----

**Dimensions**

Height	165 mm
Width	409 mm
Depth	92.50 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	0

**Dimensions**

Number of width units	18
-----------------------	----

**Cover, door**

Door/cover is transparent	Yes
---------------------------	-----

**Materials**

Material	Plastic
RAL code	9010
Colour	White

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock
Glow wire test	650 °C

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes