



936712518



Push-button, NO contact, screw terms, Integro - Design Flow/Pure, chr gl, galv

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Single rocker

Number of poles 1

Materials

Colour Chrome

Surface finish Glossy

Material Thermoplastic

Treatment Chrome plated
Coated

Transparent No

Dimensions

Height 55.50 mm

Width 55.50 mm

Depth 25 mm

Built-in depth 10 mm

Built-in depth flush-mounted boxes 13 mm

Controls and indicators

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

Safety

Ingress Protection (IP) class IP44

Impact resistance IK IK05

Accessories

Has labelling field No

Texts

Imprint Without imprint

Lighting Without lighting (cannot be illuminated)

Type of connection With screw terminals

Sustainability

RoHS conform Yes