



936712524



p-b, NO contact, screw terms, Integro - Design Flow/Pure, stain steel m, lacq

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Number of poles	1
-----------------	---

Materials

Colour	Stainless steel
--------	-----------------

Surface finish	Matt
----------------	------

Material	Stainless steel Thermoplastic
----------	----------------------------------

Treatment	Varnished
-----------	-----------

Transparent	No
-------------	----

Dimensions

Height	55.50 mm
--------	----------

Width	55.50 mm
-------	----------

Depth	24.10 mm
-------	----------

Built-in depth	10 mm
----------------	-------

Built-in depth flush-mounted boxes	13 mm
------------------------------------	-------

Controls and indicators

Number of buttons	1
-------------------	---

Type of push button	Single push button
---------------------	--------------------

With feedback signal contact	No
------------------------------	----

Safety

Ingress Protection (IP) class	IP44
-------------------------------	------

Impact resistance IK	IK05
----------------------	------

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	Without imprint
---------	-----------------

Installation mode	For screw fastening
-------------------	---------------------

Type of connection	With screw terminals
--------------------	----------------------

Sustainability

RoHS conform	Yes
--------------	-----