



936712568



Push-button, NO contact, screw terms, Integro - Design Flow/Pure, chr m, lacq

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Single rocker

Number of poles 1

Materials

Colour Chrome

Surface finish Matt

Material Thermoplastic

Treatment Chrome plated
Varnished

Transparent No

Dimensions

Height 55.50 mm

Width 55.50 mm

Depth 24.10 mm

Built-in depth 10 mm

Built-in depth flush-mounted boxes 13 mm

Controls and indicators

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

Safety

Ingress Protection (IP) class IP44

Impact resistance IK IK05

Accessories

Has labelling field No

Texts

Imprint Without imprint

Installation mode For screw fastening

Type of connection With screw terminals

Sustainability

RoHS conform Yes