



5031

Rocker push-button NO contact Module insert

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Rocker
Number of poles	1

Materials

Material	Metal Plastic
Transparent	No

Dimensions

Height	70.80 mm
Width	70.80 mm
Depth	41.60 mm
Built-in depth	30 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Texts

Imprint	Without imprint
Installation mode	With spreader claws
Lighting	For lighting and monitoring circuit
Switch mode	Normally open contact
Type of connection	With plug-in terminals

Suitable for

Berker K.x / Berker Q.x / Berker R.x / Berker S.x/B.x
