



5035



**Series push-button 2 NO contacts with common input terminal**

**Technical Features**

**Electric current**

Switching current	10 A
Momentary contact current	10 A

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Control/operation element	Double rocker
Number of poles	1

**Materials**

Material	Metal Plastic
Treatment	Untreated
Transparent	No

**Dimensions**

Height	70.80 mm
Width	70.80 mm
Depth	41.60 mm
Built-in depth	32.30 mm
Built-in depth flush-mounted boxes	35 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Controls and indicators**

Number of buttons	2
Type of push button	Series push button
With feedback signal contact	No

**Connectivity**

Type of connection	quickconnect
--------------------	--------------

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

**Accessories**

Has labelling field	No
---------------------	----

**Texts**

Imprint	Without imprint
Installation mode	With spreader claws
Lighting	For illumination
Switch mode	2NO, common input terminal
Type of connection	With plug-in terminals

**Suitable for**

K.x / Q.x / R.x / S.x/B.x
---------------------------