



5036



**Push-button change-over contact illuminated**

**Technical Features**

**Electric current**

Switching current	10 A
Momentary contact current	10 A

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Number of poles	1
-----------------	---

**Materials**

Material	Metal Plastic
Transparent	No

**Dimensions**

Height	71 mm
Width	71 mm
Depth	42 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	34 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Controls and indicators**

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

**Accessories**

Has labelling field	No
---------------------	----

**Texts**

Imprint	Without imprint
Installation mode	With spreader claws
Lighting	For lighting and monitoring circuit
Switch mode	Change-over contact, usable as NC or NO
Type of connection	With plug-in terminals

**Suitable for**

K.x / Q.x / R.x / S.x/B.x
---------------------------