



WRPS12PSB

**10AX 1 Gang 2 Way Wall Switch Polished Steel Black Insert**

**Technical Features**

**Electric current**

|                   |      |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

**Installation, mounting**

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Materials**

|                |                 |
|----------------|-----------------|
| Colour         | Silver          |
| Surface finish | Glossy          |
| Material       | Stainless steel |

**Identification**

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

**Dimensions**

|                |            |
|----------------|------------|
| Dimensions     | 86 x 86 mm |
| Built-in depth | 12 mm      |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Architecture**

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

**Texts**

|                   |  |
|-------------------|--|
| Installation mode | For flush-mounted and hollow wall mounting |
| Lighting          | Without lighting (cannot be illuminated)   |
| Switch mode       | 2-way                                      |

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |