



181110



Push-button, NO contact, TS, chrome glossy, brass galvanised

Technical Features

Electric current

Momentary contact current	1.50 A
---------------------------	--------

Voltage

Rated voltage	12 V
---------------	------

Architecture

Control/operation element	Push button
---------------------------	-------------

Number of poles	1
-----------------	---

Materials

Colour	Chrome
--------	--------

Surface finish	Glossy
----------------	--------

Material	Brass
----------	-------

Treatment	Chrome plated Galvanised
-----------	-----------------------------

Transparent	No
-------------	----

Dimensions

Height	22 mm
--------	-------

Width	22 mm
-------	-------

Depth	19.70 mm
-------	----------

Built-in depth	13 mm
----------------	-------

Built-in depth flush-mounted boxes	0 mm
------------------------------------	------

Controls and indicators

Number of buttons	1
-------------------	---

With feedback signal contact	No
------------------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Impact resistance IK	IK07
----------------------	------

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-20 - 60 °C
-----------------------	-------------

Texts

Imprint	Without imprint
---------	-----------------

Installation mode	For screw fastening
-------------------	---------------------

Switch mode	Normally open contact
-------------	-----------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----