



181110



Push-button, NO contact, TS, chrome glossy, brass galvanised

Technical Features

Electric current

Momentary contact current	1.50 A
---------------------------	--------

Voltage

Rated voltage	12 V
---------------	------

Architecture

Control/operation element	Push button
Number of poles	1

Materials

Colour	Chrome
Surface finish	Glossy
Material	Brass
Treatment	Chrome plated Galvanised
Transparent	No

Dimensions

Height	22 mm
Width	22 mm
Depth	19.70 mm
Built-in depth	13 mm
Built-in depth flush-mounted boxes	0 mm

Controls and indicators

Number of buttons	1
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-20 - 60 °C
-----------------------	-------------

Texts

Imprint	Without imprint
Installation mode	For screw fastening
Switch mode	Normally open contact
Type of connection	With plug-in terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes